


The 6018 input module has eight channels, each with programmable constant current excitation, programmable gain instrumentation amplifier, low pass filter and sample and hold. The high level outputs are multiplexed and digitized to 16 bits then output to the 6000 data bus. Each channel has a wideband analog output.

The 6018 is used with RTDs, potentiometers and low-level voltages. Each channel has a highly-stability constant current transducer excitation supply that is programmable from 0.5 to 5mA. A four wire input provides individual signal and excitation leads for high-accuracy measurements. Resistance substitution is provided for calibration of RTDs and other resistive transducers.

Voltage substitution is provided for channel gain calibration utilizing an external voltage standard. A calibration attenuator enables the voltage standard to be used on its highest accuracy ranges and provides a post-attenuator output on the rear panel for calibration. Using Pacific's PI660 software zero and gain calibrations are automatic.

The four-pole, low-pass filter uses an easily changed plug-in module to set bandwidth. Either the wideband or filtered output may be digitized and sent to the 6000 data bus. Two programmable alarms with upper and lower limits are checked each time the outputs are digitized. High-level analog outputs provide a means to independently monitor or record each channel.



FEATURES

- RTDs, potentiometers and other current excited transducers
- Programmable current excitation
- Gains 1 to 5,000 with 0.05% accuracy
- Automatic zero and gain calibration
- Four-pole, low-pass filter
- 10 kS/s with 16-bit ADC
- Programmable alarm levels
- Analog outputs

SPECIFICATIONS

RTD INPUT

Type10 Ohms to 1000 Ohms.
Configuration4 Wire with shield.

VOLTAGE INPUT

Range ±2 mV to ±10 Volts.
ConfigurationDifferential, 2 wire with shield.

INPUT

Impedance50 Megohms, shunted by 1,000 pf.
Protection.....±50 Volts differential, ±50 Volts common mode.

EXCITATION

Current.....Programmable current from 0.5 mA to 5 mA, ±0.05% in 0.5 mA steps. A short on one channel will not affect other channels.

Compliance10 Volts.
Stability.....±0.01%, ±0.005%/°C.

CALIBRATION

Resistance.....Substitution of precision calibration resistor. 100 Ohm ±0.1% supplied.
VoltageAlternate input for external calibration reference. Programmable attenuation steps of 1, 0.1, and 0.01 with ±0.01% accuracy. Output of the attenuator is provided on a rear panel connector for calibration.

ZeroAmplifier input disconnected and shorted.

AMPLIFIER

GainProgrammable steps are 1, 2, 3, 5, 10, 20, 30, 50, 100, 200, 300, 500, 1,000, 2,000, 3,000 and 5,000 with ±0.05% accuracy.

Gain Stability..... ±0.01%, ±0.005%/°C.
Bandwidth.....1 kHz (-3dB).
Linearity.....±0.01% for gains <1,000, ±0.02% for gains 1,000 and higher.

Common Mode80 dB plus gain in dB up to 110 dB, DC to 60 Hz.

CM Voltage.....±10 Volts.
ZeroAutomatic to ±1µV RTI, ±0.5 mV RTO.

Zero Stability.....±5µV RTI, ±1 mV RTO, ±1µV/°C RTI. ±0.2 mV/°C RTO. Short term: ±2µV RTI, ±0.4 mV RTO for 8 hours.

Source Current±2nA, ±0.01nA/°C.
Noise (10 Hz)0.1 µV RMS, RTI.
Noise (1kHz)1.0 µV RMS, RTI.
Recovery.....800 µS to ±0.1% for 10X overload to ±10 Volts.
Analog Output±3.0 Volt full scale, unfiltered.

FILTER

TypeFour-pole, low-pass Butterworth.
Frequency.....Plug-in, 4Hz to 1kHz, 10 Hz supplied
Noise1.0 mV RMS RTO.

SAMPLE & HOLD, ADC

Sample.....Simultaneous, within ±50 nS channel to-channel. Droop is less than ±0.005%.
Resolution16 bits, two's complement output.
Sample Rate10 KS/s per channel.
Linearity±2 LSB (±0.006%).
Continuity.....Monotonic to 15 bits.

GENERAL

Mounting.....Occupies one slot in Series 6000 enclosures
ConnectorsInput connector is 50-pin Type D, output connector is 9-pin Type D. Connectors are mounted on the front and mates are supplied.
Temperature0°C to +50°C operating.

SCREW TERMINAL ADAPTER (6081)

Termination8 channels, screw clamp terminals for inputs and outputs, #18 to #28 wire.
Mounting.....Installs on the front of the input module behind the enclosure door. Cables route to the rear through the enclosure's cable tray.

ORDERING INFORMATION

6018Eight-Channel Instrumentation Amplifier Digitizer, 10 kS/s, 16-bits.
6081Screw Terminal Adapter.